



ARCHITECTURAL & ENGINEERING SPECIFICATION

Complete EcoVantage® high efficiency 0.5 gpf sensor actuated, battery powered, wall mounted commercial urinal system with Z5755-U Omni-Flo top spud urinal, ZER6003AV-EWS-SM exposed, sensor activated chrome-plated closet diaphragm flushometer for either left or right hand supply manufactured by Zurn.

PRODUCT FEATURES

- 0.5 gpf (gallons per flush)
- Wall mounted extended rim top spud urinal
- High efficiency siphon washout flush action
- Integral trap
- Vitreous china wall urinal construction
- Diaphragm- type flushometer complete with Zurn's Go Blue® TPE, chloramine resistant, dual seal diaphragm with a clog resistant, triple filtered bypass
- High pressure vacuum breaker with one piece hex coupling nut
- Adjustable tailpiece
- True mechanical override button
- Control stop with internal siphon guard protection, sweat solder kit and wall flange with set screw
- Asymmetric back wall for reduced splash back
- Oversized footprint to make retrofit easy
- Vandal resistant outlet strainer included
- 50% water savings over standard 1.0 gpf system

COMPLIANCE AND CERTIFICATION:

Meets the American Disabilities Guidelines and ANSI A117.1 requirements when installed according to these requirements.

- Fixture - Complies with ASME A119.2 / CSA B45.1
- Flush Valve - Complies with ASSE 1037 / ASME A112.1037 / CSA B125.37



This product should be used with a WaterSense labeled counterpart with a compatible flow volume to ensure that the entire system meets the requirements for water efficiency and performance.



This system complies with the Buy American Act: Valve manufactured in the United States; Fixture manufactured in China.



ZURN ONE SYSTEM PACKOUT INCLUDES:

FIXTURE - Z5755-U:

0.125 gpf [0.5 lpf] to 1.0 gpf [3.8 lpf] vitreous china, wall hung, integral trap, washdown urinal complete with 3/4" [19mm] top spud connection, concealed universal retrofit wall bracket, 2" [51mm] outlet connection and vandal resistant outlet strainer


FLUSH VALVE - ZER6003AV-EWS-SM:

Exposed, quiet diaphragm-type, chrome-plated flushometer valve with a polished exterior. Complete with Zurn's AquaVantage® TPE, chloramine resistant, dual seal diaphragm with a clog resistant, triple filtered bypass. The valve incorporates a 6VDC motor actuator, a battery powered automatic sensor, chrome-plated metal cover with manual override push button and 10 degree angled sensor


ARCHITECTURAL & ENGINEERING APPROVAL

The information contained in this document is subject to change without notice. Please contact Zurn for most up to date information.

Rough-in / Overview dimensions



UNIVERSAL RETROFIT
BRACKET (UB)



SECTION A-A

