



191



191PC



191PC-AP

Disposal Description

- 1/3 HP permanent magnet motor delivers 1900 RPMs of grinding power and helps reduce jams
- 191 & 191PC feature EZ Mount system
- 191PC-AP feature EZ Mount to 3 Bolt Adapter Kit, fits most existing 3-bolt systems and prevents wasted time installing new flange
- Compact, lightweight design saves space
- Safe to use with properly sized septic tanks

EZ Mount	EZ Mount	EZ Mount to 3 Bolt Mount Adapter	Mount type
No	Yes	Yes	Pre-installed power cord
Yes	Yes	No	Removable Splashguard

Dimensions

191, 191PC



191PC-AP



Specification Details	
Motor Horsepower	1/3 H.P.
R.P.M.	1900
Internal grind Component Material	Galvanized Steel
Warranty	Two Year Limited
Voltage, HZ	115, 60
Current-Amps	4.0
Motor Type	Permanent Magnet
Drain Connection Size	1-1/2 in drainpipe
Dishwasher Compatibility	7/8 inch rubber dishwasher drain hose
Maximum Sink Thickness	1/2 inch
Sink Flange Material	Celcon
Sink Flange Finish	Polished Stainless Steel
Feed	Continuous
Grind Chamber Material	Reinforced Polymer
Overload Protector	Manual Reset Type – front mounted

Two Year Limited Warranty

If the disposal develops a material or mechanical defect during the warranty period, Whirlaway will repair or replace it free of charge.

For more information call 1-800-854-3229