

## 6" Deluxe Universal Housings



### IC Housing

Energy-efficient, Air-Loc® double wall housing can be covered with insulation. Includes Real Nail® 3 bar hangers.

**IC2** 6" IC new Construction Housing  
**IC2 G** with pre-installed Air-Loc gasket  
**IC2 W** with push-in electrical connectors  
**IC2 W G** with push-in electrical connectors and pre-installed Air-Loc gasket

17 $\frac{1}{8}$ " L x 9 $\frac{1}{8}$ " W x 7 $\frac{1}{2}$ " H  
 Ceiling cutout: 6 $\frac{1}{8}$ "



### TC Housing

Requires 3" spacing from insulation. Includes Real Nail® 3 bar hangers (unless otherwise noted).

**TC2** 6" Non-IC New Construction Housing  
**TC2 S** with smaller footprint bar hangers  
 Real Nail® 2)  
**TC2 W** with push-in electrical connectors

13 $\frac{1}{8}$ " L x 7 $\frac{1}{2}$ " W x 7 $\frac{1}{2}$ " H  
 Ceiling cutout: 6 $\frac{1}{8}$ "



### TC Remodel Housing

Requires 3" spacing from insulation. Installs from below ceiling.

### TC2R Remodel Housing

13 $\frac{3}{4}$ " L x 7 $\frac{1}{16}$ " W x 5 $\frac{1}{4}$ " min H;  
 7 $\frac{1}{4}$ " max H  
 Ceiling cutout: 6 $\frac{3}{4}$ "

**Note:** In Canada when insulation is present, Type IC fixtures must be used.


## 6" Deluxe Universal Trims

### Downlights



#### Tapered Baffle\*

24 WWH White  
 24 BBL Black  
 24 BWH Black  
 24 BABZ Black  
 24 BSC Black  
 75W PAR30L,  
 65W BR30  
 5 $\frac{1}{4}$ " Aperture




#### Pinhole with Baffle

23 BWH Black  
 50W R/PAR20  
 3 $\frac{1}{8}$ " Aperture



#### Straight Cone

26 BWH Black Alzak®  
 26 CWH Clear Alzak®  
 26 GWH Gold Alzak®  
 26 HZWH Haze  
 26 PTSC Pewter Alzak®  
 26 WWH Gloss White  
 26 WHZWH Wheat Haze  
 IC: 90W PAR38, 85W BR40  
 TC: 150W PAR38,  
 120W BR40  
 5 $\frac{1}{4}$ " Aperture



#### Straight Baffle

25 WWH White  
 25 BWH Black  
 25 BBL Black  
 25 BSC Black  
 IC: 85W BR40, 90W PAR38  
 TC: 150W PAR38, 120W  
 BR40  
 5 $\frac{1}{4}$ " Aperture



#### PAR30 Deep Baffle

254 WWH White  
 254 BWH Black  
 75W PAR30, 100W PAR38  
 5 $\frac{1}{8}$ " Aperture



#### Tapered Cone\*

27 BWH Black Alzak®  
 27 CWH Clear Alzak®  
 27 GWH Gold Alzak®  
 27 HZWH Haze  
 27 PTSC Pewter Alzak®  
 27 WWH Gloss White  
 27 WHZABZ Wheat Haze  
 27 WHZWH Wheat Haze  
 75W PAR30L, 65W BR30  
 5 $\frac{1}{8}$ " Aperture



#### PAR30 Deep Cone

257 BWH Black Alzak®  
 257 CWH Clear Alzak®  
 257 GWH Gold Alzak®  
 257 HZWH Haze  
 257 WHZWH Wheat Haze  
 75W PAR30, 100W PAR38  
 5 $\frac{1}{8}$ " Aperture



#### BR40/R40 Open Frame

251 WH  
 IC: 100W BR40  
 TC: 120W BR40, 250W R40  
 Heat Lamp  
 5 $\frac{1}{8}$ " Aperture



#### BR30 Open Frame

250 ABZ  
 250 SC  
 250 WH  
 65W BR30  
 4" Aperture

### Trim Ring Finishes

**ABZ** Classic Aged Bronze

**SC** Satin Chrome

**WH** White

**BL** Black

### Housing Accessories

Catalog Number	Description
<b>ALG6</b>	Energy Conserving Gasket for 6" New Construction Air-Loc® IC Housings
<b>G2405</b>	T-Bar Clips (Set of 4) for TC2 S
<b>TR6 ABZ</b> <b>TR6 SC</b> <b>TR6 WH</b> <b>TR6 BL</b>	6" Trim Ring compatible with 24, 25, 26, 27, 254 and 257 trims

\* Trim may be used with TC2R housing adjusted in lowest (5-1/4") height position.

# 6" Standard Universals

Standard Universal downlights are offered with basic trim options but include all the installation and performance features Juno is known for.

## 6" Standard Universal Housings



### IC Housing

Energy-efficient, Air-Loc® housing can be covered with insulation. Includes Real Nail® 3 bar hangers (unless otherwise stated).

- IC22** 6" IC New Construction Housing
- IC22 G** with pre-installed Air-Loc gasket
- IC22 S** with smaller footprint bar hangers (Real Nail® 2)
- IC22 S G** with smaller footprint bar hangers (Real Nail® 2) and pre-installed Air-Loc gasket
- IC22 W** with push-in electrical connectors
- IC22 W G** with push-in electrical connectors and pre-installed Air-Loc gasket

13¼" L x 7½" W x 7⅞" H  
Ceiling cutout: 6⅞"



### IC Remodel Housing

Energy-efficient, Air-Loc® housing can be covered with insulation. Installs from below ceiling with clips provided.

### IC22R 6" IC Remodel Housing

13¼" L x 7⅞" W x 7⅞" H  
Ceiling cutout: 6¾"

## 6" Standard Universal Trims

### BR/PAR Downlights



#### Tapered Cone

- 27 BWH Black Alzak®
- 27 CWH Clear Alzak®
- 27 GWH Gold Alzak®
- 27 HZWH Haze
- 27 PTSC Pewter Alzak®
- 27 WWH Gloss White
- 27 WHZABZ Wheat Haze
- 27 WHZWH Wheat Haze
- 50W PAR30, 65W BR30, 75W PAR30L
- 5¼" Aperture



#### Tapered Baffle

- 24 WWH White
- 24 BWH Black
- 24 BABZ Black
- 24 BBL Black
- 24 BSC Black
- 75W PAR30L, 50W PAR30, 65W BR30
- 5¼" Aperture



#### Shallow Baffle

- 244S WWH White
- 244S BWH Black
- 60W PAR30, 65W BR30, 75W PAR30L
- 5¼" Aperture



#### Straight Baffle

- 25 WWH White
- 25 BBL Black
- 25 BABZ Black
- 25 BWH Black
- 25 BSC Black
- 50W PAR30, 65W BR30
- 5¼" Aperture



#### Ultra-Trim Cone - Fully Enclosed\*

- (Wet Location w/ Outdoor Lamps)
- 29 CWH Clear Cone
- 29 WWH White Cone
- 60W A19, 65W BR30, 75W PAR30/30L, 90W PAR38/BR40
- 5½" Aperture



#### BR30 Open Frame

- 250 ABZ
- 250 SC
- 250 WH
- 65W BR30
- 4" Aperture



#### Shallow Cone

- 247S BWH Black Alzak®
- 247S CWH Clear Alzak®
- 247S GWH Gold Alzak®
- 247S HZWH Haze
- 247S WHZWH Wheat Haze
- 75W PAR30L, 65W BR30, 75W PAR30
- 5¼" Aperture



#### BR30 Regressed Open Frame

- 252 WH
- 65W BR30
- 4" Aperture



#### Ultra-Trim Baffle - Fully Enclosed\*

- (Wet Location w/ Outdoor Lamps)
- 28 WWH White
- 28 BWH Black
- 60W A19, 65W BR30, 75W PAR30/30L, 90W PAR38/BR40
- 5½" Aperture

### Adjustables



#### Cylinder Spotlight in Baffle

- 226 WWH White
- Cylinder in White Baffle
- 226 BWH Black
- Cylinder in Black Baffle
- 60W PAR16



#### R/PAR20 Regressed Eyeball

- 228 WH
- 50W R/PAR20

#### R/PAR20 Regressed Eyeball in Baffle

- 248 WWH White
- 50W R/PAR20



#### PAR/BR30 Regressed Eyeball

- 229 ABZ
- 229 BL
- 229 SC
- 229 WH
- 75W PAR30L, 65W BR30

#### PAR/BR30 Regressed Eyeball in Baffle

- 249 WWH White
- 249 BWH Black
- 75W PAR30L, 65W BR30