



PIP® ChemFR™

Treated PVC Two-Piece Acid Suit - 0.40 mm

- Special PVC layered material provides protection against various liquid splashes and incidental contact
- Vented cape back and underarm vents for a wide range of motion and comfort
- Four snap front closure
- Attached drawstring hood for secure fit
- Open wrist with adjustable snap closures
- Two flap pockets to secure valuables
- Overalls have open ankles with adjustable snap closures
- Adjustable suspenders with triangular buckles and studs
- Snap to fit sizing at the waist for a secure fit
- Not designed for use in an ARC flash or flash fire application
- Treated to provide limited flammability and is self-extinguishing (ASTM D6413 test method)
- ⚠ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Road Work
- Municipal
- Shipyards
- Railyard
- Agriculture
- Plant Maintenance
- Not designed for use in an ARC flash or flash fire application



P65

Technical Data

Color	Green
Sizes Available	M-4XL
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	20.25 x 14.50 x 6.75
Case Weight (lbs)	26.46
Country of Origin	China
Fabric	Polyester, PVC
Thickness	0.4 mm
Total Pockets	2
Pocket Type	Flap Pocket
Hood	Attached
Closure	Snap
Construction	Water Resistant, Underarm Vents, Cape Vented Back
Certifications	ASTM D6413

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
4045/M	Green	M	662909404565		10662909404562
4045/L	Green	L	662909404510		10662909404517
4045/XL	Green	XL	662909404527		10662909404524
4045/XXL	Green	2XL	662909404534		10662909404531
4045/XXXL	Green	3XL	662909404541		10662909404548
4045/XXXXL	Green	4XL	662909404558		10662909404555