

NATALIA

H999102-AGB/CYD

Inspired by the look of stone, the Natalia sconce has an organic, flexuous form with an all-over earthy ceramic Windy Dune finish. The soft, weathered texture brings the expressive shape to life, lending a found-object look. Equipped with two lights and Aged Brass inner hardware, this petite sconce serves as a unique wall washer that can be used in a variety of spaces.

FINISHES

AGED BRASS w/ Ceramic Windy Dune

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 11.5"

Width/Diameter: 6.75"

Canopy/Backplate: 4.75"

Product Weight: 7lb

Extension: 4.5"

Top to Center: 7.75"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 2

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 24" x 14" x 13"

Carton 1 Weight: 11lb

Shipping Method: Ground

Country of Origin: VN

