

Watertight Devices, Twist-Lock® Plug, 30A, 3 Phase 250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L15-30P, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL28W75](#)

PLUG, W/TIGHT, 3P 30A, 250V, L15-30P,YL



Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

Performance

Electrical - Current Interrupting - Rated for current interruption per UL498, Electrical - Dielectric Voltage - 2500V AC, Electrical - Max Working Voltage - As marked, Electrical - Temperature Rise - 30°C max per UL498 at rated current, Environmental - UV resistance - All exposed materials are UV stabilized, Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P, Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous, Mechanical - Cord Accommodation - 0.375"-1.000" (9.5-25.4)

Specifications

Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Contact Manufacturer
Nema Rating	L15-30P
Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards

Conductor

Number Of Wires	4-Wire
Wire Size	<ul style="list-style-type: none"> • Min Cords: 12/3 SJ, 16/3 S, 14/4 SJ, 18/4 S, 18/5 S

- Max Cord: 8/3 S, 8/4 S, 10/5 S

Number Of Poles

3-Pole

Current

Amperage Rating	30 A
Voltage Rating Description	3 Phase 250 VAC
Voltage Rating	3 Phase 250 VAC
Current / Amperage Rating	30 A

Dimensions

Length	2.77 in
Height	3.94 in
Width	2.77 in
Dimensions	2.77 in x 2.77 in x 3.94 in

General

Color	Yellow
UPC	783585131719
Type	Plugs
Item Type	30A Watertight Twist-Lock® Plug

Logistics

Pallet Quantity	660
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)