

WEDGEWOOD

MDS2200-AGB/OW

FINISHES

AGED BRASS w/ OFF-WHITE (MDS)

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 17"

Width/Diameter: 8"

Canopy/Backplate: 4.75"

Product Weight: 1.914lb

Extension: 9"

Top to Center: 14.5"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: Yes

Shade

Shade 1: Fabric

Shade 1 Finish: White Linen 1

Shade 1 Top Width: 4"

Shade 1 Bottom L/W: 0" / 8"

Shade 1 Height: 6"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 20" x 20" x 11"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: VN

