Project / Job Name:

Location:

Fixture Type:

Notes:



62-8028 - Silhouette LED Island Pendant; 71 Watt; 2700K/3000K/3500K CCT; Smoked Bronze Finish

90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 25,000 HOURS | 3 YEAR WARRANTY | 120-277V | IP 20

GENERAL

Company	NUVO
EA Height	12.99
EA Width	9.64
EA Length	68.11
Mounting Height	1.38
Mounting Length	65.38
Mounting Width	6.63
Bulb Included	Integrated
Material	Steel
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<10%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Silhouette
Finish Family	Bronze
Amps	1.800A
Lens Finish	Amber
Lens Material	Glass
Lensed	Yes
Power Factor	>0.9
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	190W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K
Dimmable	Yes-Dimmable
Hours Rated	25000
Beam Angle (degree)	120
Color Temp	Warm White to Neutral White
CRI	90+
Dimming Type	Phase cut
Operating Frequency	50/60Hz
Operating Temp	-4F to +140F (-20C to +60C)
Lumens	5680L
Volts	120V-277V
Watts	71W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Bronze
Housing Color	Smoked Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Cylinder

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416583
Case Cube	4.9358
Case Height	12.99
Case Length	68.11
Case Quantity	1
Case UPC	10045923416580
Case Weight	61.5
Case Width	9.64
EA Cube	4.9358
EA Height	12.99
EA Length	68.11
EA Quantity	1
EA Weight	61.5
EA Width	9.64
Pack Type	Kraft Box
Web Height	6.0
Web Length	62.5
Web Width	6.0

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026