



SPRF34D



34" x 23.63" x 23.75" (H x W x D)

Two-drawer refrigerator-freezer for built-in or freestanding use, with digital thermostat, frost-free operation, panel-ready drawer fronts, and complete stainless steel construction

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Unique two-drawer design features separate refrigerator and freezer compartments

Panel-ready drawers allow you to create a truly custom look for your space

Product Features:

24" Wide 2-Drawer Refrigerator-Freezer	Complete refrigeration storage solution with top drawer refrigerator and bottom drawer freezer
Built-in capable	Make the best use of space by installing this unit under the counter and flush with other cabinetry
Stainless steel construction	Interior and exterior are fully constructed from stainless steel to ensure lasting durability and easy cleanup
Panel-ready drawer fronts	Drawers accept overlay panels (size: 23.43" x 15" at 3/4" thick) to let you seamlessly blend the refrigerator into cabinetry design
Two sliding drawers	Smooth gliding stainless steel drawers for easy use
Frost-free operation	Minimum user maintenance with a fully no-frost operation system
Digital thermostat	Electronic controls located on the top drawer ensure easy temperature management, with an external readout of Celsius or Fahrenheit
LED lighting	Elegant LED lighting in a gentle white hue illuminates the refrigerator section for an easy view of the interior
Drawer dividers	Two adjustable dividers make it simple to organize the drawer interiors



Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	380.0kWh/year
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	108.0 lbs. (49 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101073262

Refrigerant Amount	1.13 oz.
High Side PSI	270.0
Low Side PSI	105.0
Freezer - Temperature Range	-11°F to 11°F
Compressor Step Height	3.5" (9 cm)
Compressor Step Width	18.75" (48 cm)
Compressor Step Depth	4.0" (10 cm)
Sabbath Mode	Yes
Sound Level	34.2 dB

