

PRODUCT DESCRIPTION

A flexible LED mirror that allows for both vertical and horizontal installation with an endless length configuration. LED light bars projecting 50% more light than your typical concealed light source match the exact dimensions of selected mirror lengths and suspend them to the wall. Additional light bars can be added to create wider mirror lengths broken up by the light source. A remote driver was created to fit within standard junction boxes for convenient installation. This economical LED mirror kit can be configured to your space requirements.

MEASUREMENTS

DIMENSION	: 24" W x 42" H x 2" Ext
HANGING WEIGHT	: 21.82 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 3,800 Rated (3,100 Del.)
BULB	: 2 x 19W LED PCB Integrated , 38W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: N
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Polished Chrome (PC)

MATERIAL

Aluminum, Acrylic, Glass

RATINGS

cETLus
Damp Location
CA Title 24

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.