

PAULETTE

H1140101-AGB/CMC

The delicately scalloped Paulette sconce embodies the spirit of new Romanticism, transforming functional lighting into artful expression. A hand-sculpted ceramic backplate creates an expressive vignette in either Gossamer Ivory, Indigo Wash, or a Moss Crackle glaze. An Aged Brass gooseneck arm introduces a heritage detail that completes this transitional fixture.

FINISHES

AGED BRASS w/ CERAMIC MOSS CRACKLE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 11.25"

Width/Diameter: 9.75"

Length: 4"

Canopy/Backplate: 5.5"

Product Weight: 4lb

Extension: 4.25"

Top to Center: 5"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Ceramic

Shade 1 Finish: Moss Crackle

Shade 1 Top Length: 1.75"

Shade 1 Top Width: 9.75"

Shade 1 Height: 9.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 14" x 12" x 7"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: VN

