



SATCO LED lamps offer one of today's largest selections of LED products — providing solutions for the commercial, industrial and residential markets.

We bring quality, value and design to every product we create. With advancing technology, we improve performance, energy savings, safety, ease of installation and maintenance, and overall satisfaction.

We are your partners in success — from convenient packaging options and retail support to inventory supply.

SATCO is the lighting solution you can count on for the products you can rely on!



LED filament lamps Globes - G16½

LED with a traditional incandescent look and feel

Omni-directional light source

Dimmable

Damp location

Approved for totally enclosed fixtures***

c-UL-us listed

CEC T20/T24 Available

ENERGY STAR certified*

3 Year warranty



S12105
G16



S12102, S12103,
S12104
G16



S12101
G16



S9870, S29871,
S29988, S8553
G16 1/2

LED Globe Filament Lamps - G16½



Item Number	Lamp Description	W	Bulb Type	Base	V	Finish	CCT	Lm	CRI	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9870	2.5G16/LED/CL/27K/120V/E12	2.5	G16 1/2	E12	120	Clear	2700K	200	80	3 3/16	15K	045923098703	24/6
S29871*	4G16/LED/CL/27K/120V/E12	4	G16 1/2	E12	120	Clear	2700K	350	80	3 3/16	15K	045923298714	24/6
S29988*	5.5G16/LED/CL/27K/120V/E12	5.5	G16 1/2	E12	120	Clear	2700K	500	80	3 1/8	15K	045923099885	24/6
S12100	4.5G16/LED/CL/3K/120V/E12	4.5	G16 1/2	E12	120	Clear	3000K	500	80	3 1/8	15K	045923121005	24/6
S12101	5.5G16/LED/W/3K/120V/E12	5.5	G16 1/2	E12	120	White	3000K	500	80	3 1/8	15K	045923121012	24/6
S12102	5.5G16/LED/CL/27K/120V/E26	5.5	G16 1/2	E26	120	Clear	2700K	500	80	3 1/8	15K	045923121029	24/6
S12103	5.5G16/LED/CL/3K/120V/E26	5.5	G16 1/2	E26	120	Clear	3000K	500	80	3 1/8	15K	045923121036	24/6
S12104	5.5G16/LED/CL/4K/120V/E26	5.5	G16 1/2	E26	120	Clear	4000K	500	80	3 1/8	15K	045923121043	24/6
S12105	5.5G16/LED/W/3K/120V/E26	5.5	G16 1/2	E26	120	White	3000K	500	80	3 1/8	15K	045923121050	24/6
90 CRI—CEC/T20													
S8553*	4G16/LED/CL/927/120V/E12	4	G16 1/2	E12	120	Clear	2700K	350	90	3 3/16	15K	045923085536	24/6
S11364*	4.5G16/LED/W/927/120V/E12	4.5	G16 1/2	E12	120	White	2700K	360	90	3 1/4	15K	045923113642	24/6
S11363*	4.5G16/LED/CL/930/120V/E12	4.5	G16 1/2	E12	120	Clear	3000K	360	90	3 1/4	15K	045923113635	24/6

Product sheet SA1980

**See warranty for details.