SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



67-125 - Combination Green Exit Sign/Emergency Light; Singe/Dual Face; 120/277 Volts; Remote Compatible; White Finish

GENERAL

Company	NUVO
EA Height	3.43
EA Width	7.56
EA Length	15.98
Bulb Included	Integrated
Material	Thermo Plastic
Fixture Type	Exit Sign
Includes	Mounting hardware and accessories
Product Notes	UL94V-0, Thermoplastic, 3.6V AA900mAh Ni-Cad Battery, 90 minutes duration, 24 hour charge time, 10C-40C, Remote Compatible; Letter Height: 6 in.; Letter Stroke: 0.75 in.; Path of Egress: 6 Ft.
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 3KV
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Additional Info	Input Wattage: 3.5W; Output Wattage: 1.5W; Energy Used in Maintenance Mode: 3.3W
Amps	0.029/0.013A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Fixture Lamp Count	2
Incandescent Equivalent	10W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5700K
Dimmable	Non-Dimmable
CRI	70+
Operating Frequency	60Hz
Operating Temp	+50F to +104F (+10C to +40C)
Lumens	150L
Volts	120V/277V
Watts	3.5W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Ceiling/Wall

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923670275
Case Cube	1.6204
Case Height	11.02
Case Length	16.34
Case Quantity	6
Case UPC	10045923670272
Case Weight	19.77
Case Width	15.55
EA Cube	0.2398
EA Height	3.43
EA Length	15.98
EA Quantity	1
EA Weight	3.23
EA Width	7.56
Pack Type	Box
Web Height	7.25
Web Length	4.0
Web Width	19.0

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	No
Title 20	Yes
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026