


PRODUCT DESCRIPTION

A water feature that seemingly flows down a narrow, elongated channel constructed of aluminum. Finished in Black the decorative plate is fabricated using 304 Grade Stainless Steel in a Polished Black finish making these impressive sconces suitable for outdoor applications.



MEASUREMENTS

DIMENSION	: 5" W x 72" H x 2.5" Ext
BACK PLATE	: 5" W x 72" H x 36" HCO
HANGING WEIGHT	: 14.8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,400 Rated (1,680 Del.)
BULB	: 2 x 30W LED AC Integrated , 60W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)

GLASS

Black Ripple 125

MATERIAL

Aluminum, Stainless Steel

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com