

CLIVEDON

MDS1401-AGB/CRN

What began as a chandelier is now an entire family of Clivedon fixtures. Featuring sharp tapered shades and heritage-inspired details, these are the new elevated basics for the modern home. With Aged Brass and either Soft Studio Green or Soft Crimson finish options, each shade is metal on the inside and painted on the outside. Available as a sconce with a gooseneck, a pendant in two sizes, and a 5-light chandelier, Clivedon is designed to suit a variety of room sizes and styles.

FINISHES

AGED BRASS w/ SOFT CRIMSON

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 6.5"

Width/Diameter: 12"

Minimum Height: 15"

Maximum Height: 110"

Canopy/Backplate: 5.25"

Hanging Type: 120" BLACK BRAIDED CORD

Product Weight: 3.52lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Metal

Shade 1 Finish: Soft Crimson

Shade 1 Top Width: 2.5"

Shade 1 Bottom L/W: 0" / 12"

Shade 1 Height: 4.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: G25

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Wire Length: 120"

Cord Type: SVT BLACK FABRIC

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 16" x 16" x 10"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: VN

