

Installing the wick in the Extra Bright Lamp

Page 1

Step 1: Look at the photo in in step one. If the wick on both ends is heavily frayed, Trim it just a bit. **NO NOT CUT THE LENGTH! JUST REMOVE THE FRAYED AREA.**

Step 2: After removing the wick assembly described in the how to fill document, notice the bottom area has a large U shaped opening.

Step 3: Fold the end of the wick into a U shape as pictured in photo 3. and insert it int the assembly. It is important that you get it in evenly. If one side is in deeper than the other it will wind in crooked.

Step 4: Turn the wick advancing knob clockwise and advance the wick, If it begins to go in crooked Back it out and try again. Continue to advance the wick until it is above the brass tube about a 1/6th inch. Fill the oil tank about 3/4 of the way with **Lamp Oil** or **Kerosene**. **DO NOT USE ANY OTHER FUEL.** Feed the wick into the fuel reservoir and thread the wick assembly onto the tank. Allow about one hour for the wick to absorb the fuel . Once the fuel is absorbed, the wick should be wet will fuel. Light the wick and adjust the flame a bit higher. **NOTE**, advancing the wick higher will brighten the light, however, too high and it will starve the wick of fuel and start burning the wick. If you need further assistance contact Garrett Wade customer service @ 800-221-2942

Installing the wick in the Extra Bright Lamps

Page 2

