



SCR1301LHD



72.75" x 23.38" x 25.25" (H x W x D)

Commercial glass door beverage center with lock and left hand door swing

Highlights:

Made in Denmark

Commercially approved to NSF-7 standards

LED lighting inside door panel offers an attractive and efficient view

Product Features:

Upright beverage center	Commercial merchandiser made in Denmark
Commercially approved	ETL-S listed to ANSI-NSF Standard 7 for use in commercial establishments
Thin-line design	Limited space is no problem for our thin-line models, designed specifically for those hard-to-fit spots
Double pane tempered glass door	Tropicalized design protects contents from ambient hot temperatures
Automatic defrost	Reduced maintenance with auto defrost system
LED lighting inside door	Door panel features a full-length LED strip to provide an attractive and energy efficient presentation
Heavy duty adjustable shelves	Slide-out shelves with no clips for faster adjusting, with a 79 lb. capacity to hold multiple beverages as needed
Bottom shelf	Additional shelf sits on the floor to keep items raised from the unit's interior bottom
Powerful fan-forced cooling	Two fans help to ensure even temperature distribution throughout the interior



SCR1301LHD Specifications:

Overview	
Nominal Height	73.0" (185 cm)
Height of Cabinet	72.75" (185 cm)
Nominal Width	24.0" (61 cm)
Width	23.38" (59 cm)
Nominal Depth	26.0" (66 cm)
Depth	25.25" (64 cm)
Depth with Handle	26.75" (68 cm)
Depth with door at 90°	46.38" (118 cm)
Capacity	12.4 cu.ft. (351 L)
Defrost Type	Automatic
Door	Glass
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	2.4
Voltage/Frequency	115 V AC/60 Hz
Weight	184.0 lbs. (83 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101089614
Refrigerator Features	
Door Swing	LHD
Reversible	No
Shelf Type	Wire
Shelf Qty	5
Adjustable Shelves	Yes
Thermostat Type	Digital
Refrigerant Type	R600a
Refrigerant Amount	1.76oz.
High Side PSI	430.0
Low Side PSI	87.0
Interior Light	Yes
Temperature Range	32 to 50°F
Sound Level	34.6 dB
Dimensions	
Interior Height	62.75" (159 cm)

Interior Width	20.63" (52 cm)
Interior Depth	17.5" (44 cm)
Compressor Step Height	8.25" (21 cm)
Compressor Step Width	20.63" (52 cm)
Compressor Step Depth	7.0" (18 cm)

