

KENTON

C4418-VGL

Wrapped in bleached abaca, a minimalist flush mount silhouette becomes a textural statement piece. The wide circular frame of Kenton is fitted with a glossy opal glass diffuser, emanating soft light across a large area. Available in two sizes, the warming shades of Kenton illuminate modern, coastal, or transitional interiors.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 5"

Width/Diameter: 17.75"

Canopy/Backplate: 8.75"

Product Weight: 9.9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Abaca

Shade 1 Top Width: 15"

Shade 1 Bottom L/W: 0" / 17.75"

Shade 1 Height: 4.25"

Shade 2: Glass

Shade 2 Finish: Opal Glossy

Shade 2 Top Width: 8.25"

Shade 2 Height: 3.25"



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Bulb Type: LED

Max Wattage: 12

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 850

Title 24: No

Field Serviceable: Yes

SHIPPING

Carton 1: 22" x 22" x 13"

Carton 1 Weight: 17lb

Shipping Method: Ground

Country of Origin: PH

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993