



Project / Job Name:

Location:

Fixture Type:

Notes:

S14339 - 15 Watt LED A19; 4000K CCT; Medium Base; Plastic; 120 Volt; 4-Pack



GENERAL		
Company		SATCO
EA Height		5.35
EA Width		2.4
EA Length		6.46
Material		Plastic
Fixture Type		Miniature
Status		Active
Surge Protection		Built-in-surge protection - 0.5KV
Total Harmonic Distortion		<150%
CCT Selectable		No
Wattage Selectable		No
Finish Family		White
Amps		0.230A
IOT Enabled		No
Lens Finish		Frosted
Lens Material		Plastic
Lensed		Yes
Operating Position		Universal
Power Factor		>0.5
SDS Class		LED_Lamp
Indoor Outdoor		Indoor and Outdoor
Product Technology		LED
Incandescent Equivalent		100W

ELECTRICAL		
CCT (Kelvin Temp)		4000K
Dimmable		Non-Dimmable
Hours Rated		15000
Beam Angle (degree)		180
Color Temp		Cool White
CRI		80+
Operating Frequency		60Hz
Operating Temp		-4F to +104F (-20C to +40C)
Lumens		1600L
Volts		120v
Watts		15W

PHYSICAL		
Lamp Base		Medium
Finish		Frost
Housing Color		White
ANSI Base		E26
Lamp Type		A19
MOD Lamps		2.32
MOL		4.45

ADDITIONAL INFO		
Warranty		2-Years
Rated For Enclosed Fixture		Yes

FEATURES		
Flicker Free		Yes

PACKAGING		
UPC		045923143397
Case Cube		0.7294
Case Height		11.5
Case Length		13.7
Case Quantity		12
Case UPC		10045923143394
Case Weight		5.04
Case Width		8.0
EA Cube		0.048
EA Height		5.35
EA Length		6.46
EA Quantity		1
EA Weight		0.37
EA Width		2.4
Pack Type		Color Box
Web Length		4.45
Web Width		2.32

COMPLIANCE		
ADA Compliant		No
CA Prop 65		Lead
Dark Sky Rated		No
FCC Compliant		Yes
IP Rating		IP20
Location Rating		Damp
NSF Approved		No
ROHS Compliant		Yes
Safety Listing		cETLus - Listed
California Ban		Non-Compliant
Title 20		No
T24/JA8 Compliant		No
US State Ban		CA