



	NET WEIGHT	PACKAGED WEIGHT
	21.52LB/9.76KG	26.23LB/11.9KG

ELECTRICAL SPECIFICATIONS OF LIGHT:
 OUTPUT: 30W / 15W (100% / 50%)
 INPUT: 120VAC 60Hz
 LUMINOUS FLUX(LM): 130LM/W±10%
 CCT: 5000K
 BEAM ANGLE: 30°
 IP GRADE: IP65
 1FT CABLE WITH NEMA 5-15P US PLUG

ELECTRICAL SPECIFICATIONS OF 40" SINGLE ARM:
 5FT CABLE WITH NEMA 5-15P US PLUG
 INTEGRATED 2X RECEPTACLES & 1X SWITCH

ELECTRICAL SPECIFICATIONS OF 18" FAN:
 OUTPUT: 100W
 INPUT: 120VAC 60Hz
 MATERIAL: METAL GRILLES, 3 ALUMINUM BLADES, METAL GUARD, METAL BRACKET
 MOTOR: 100% ALUMINUM WIRE
 AIR VELOCITY: 6.5M/S
 SPEED SETTINGS: 1050/ 1150/ 1300RPM
 6FT CABLE WITH NEMA 5-15P US PLUG

TOL ±	GENERAL TOL:				
RANGE	0.1	0.15	0.2	0.3	0.4
0~10	0.1	0.15	0.2	0.3	0.4
10~30	0.15	0.2	0.25	0.3	0.4
30~50	0.2	0.3	0.35	0.4	0.6
50~100	0.25	0.4	0.4	0.5	0.8
100~	0.3	0.5	0.6	0.8	1.0
ANGLE	1°	2°	3°	3°	5°
SCALE	1	SCALE	UNIT	PAPER	
1:1	1/1	mm	A4		



DRAWING NO: 60-1059
 PART NAME: FANDL40SA-A30W
 MATERIAL NO: