

MALTBY

RTL8613-TBK

The Maltby lantern is designed to adapt to a variety of outdoor living areas, bringing light where hardwired fixtures aren't possible. Wrapped in woven polypropylene cord and finished in Textured Black, it is weather-resistant, stylish, and built to last. Available in two sizes, the lanterns can be used alone as a table lamp, hung on a small or large wall hook as a sconce or placed on a lamp stand for ambient lighting. Simply remove and recharge the battery-powered LED when needed.

*The Small Wall Sconce Hook is not compatible with the Large Table Lamp

FINISHES

TEXTURE BLACK

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12.5"

Width/Diameter: 10"

Canopy/Backplate: 3.75"

Product Weight: 3lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: All Weather String

Shade 1 Top Width: 10"

Shade 1 Height: 10"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 7

Bulb Quantity: 1

Wire Length: 60"

Cord Type: BLACK FABRIC USB-C CHARGING CORD

Switch Type: TOUCH DIMMER

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 25

Title 24: No

Field Serviceable: No



Battery

Battery Powered: Yes

Battery Included: Yes

Battery Life: 12-15 Hours

SHIPPING

Carton 1: 14" x 14" x 15"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: VN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993

MALTBY

RTL8613-TBK
