
28W White Outdoor Dual Head Integrated LED Flood Light

Features

- Bright long-lasting LEDs are integrated into the fixture so there are no bulbs to replace
- Wet location rated suitable for use in open-air decks and patios, uncovered porches and walk-ways
- Weather and rust-resistant housing with UV-protected, shatter resistant lens provides enhanced durability
- **Ideal usage:** Security Fixture
- **Special Features:** Weatherproof, Shatter Resistant, Adjustable Head



Specifications

Item Number	Item Length (In)	Item Width (In)	Item Height (In)
S9DFL/850/WH	4.5	7.7	4.5
Fixture Type	**Fixture Finish**	**Fixture Lens Material**	**Fixture Mount**
Security	Polycarbonate	Polycarbonate	Pole
Fixture Color	**Technology**	**Brightness (LUMENS)**	**Lumen Efficiency (LPW)**
White	LED - SMD	2000	71.43
Beam Angle	**Color Accuracy (CRI)**	**Color Temperature (CCT)**	**Life Hours**
110	80	5000	50000
Life Years	**Voltage (V)**	**Annual Energy Cost ($)**	**Energy Used (Wattage)**
17	120	3.37	28
Battery Operated	**Pack Quantity**	**Smart**	**Portable**
No	1	No	No
Dimmable	**Hardwire**	**Enclosed Fixture Rated**	**Safety Location**
No	Yes	No	Wet
CEC Compliant	**Warranty Years**		
Not Regulated	5		