Luna | E25212-CHK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

MEASUREMENTS

DIMENSION	: 9.5" L x 9.5" W x 12.5" H
MAX OAH	: 58.5" OAH
CANOPY	: 5" W x 1" H x 5" L
HANGING WEIGHT	: 19.4 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 500 Rated (400 Del.)
BULB	: 1 x 6W LED E26 Medium , 6W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Chaulk White (CHK)

MATERIAL

Concrete, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com