

Garant**Micro-boring head Ø 0.3 - 19.1 mm:****Order data**

Order number	237495
GTIN	4045197681416
Item class	29W

Description**Version:****Adjustment accuracy 0.01 mm per graduation / with vernier 0.002 mm on the Ø.****Application:**

With cutting insert No. 237621, adapter No. 237624 and insert No. 237625.

Technical description

Reach L ₁	32 mm
External Ø D ₁	32 mm
Shank Ø D ₂	16 mm
Ø D ₃	7 mm
Through-coolant	yes
Type of product	Boring tool