
# **Diaphane** | E11032-95BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



## PRODUCT DESCRIPTION

Hexagonal tubes of various lengths support blocks of naturally translucent rock crystal. Each stone varies in diaphaneity making a unique display of refracted light. Available in a plated soft Gold or Matte Black, this luxurious LED pendant light cluster and coordinating wall sconce accentuates the beauty of the natural quartz material.




*max overall height

### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 27.5" L x 27.5" W x 23.75" H |
| MAX OAH | : 145" OAH |
| CANOPY | : 27.5" W x 1.75" H x 27.5" L |
| HANGING WEIGHT | : 31.97 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 5,200 Rated (3,380 Del.) |
| BULB | : 12 x 5W LED PCB Integrated , 60W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : Only at 120V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |

### FINISHES OPTION

Black (BK)

Gold (GLD)

### GLASS

Rock Crystal 95

### MATERIAL

Rock Crystal, Steel

### RATINGS

cETLus
Dry Location

### ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.


ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com