

ESL – Escalate™ Stairwell Luminaire*

Escalate offers an attractive, intelligent solution to stairwell lighting. Certified to UL924 standards and available with with occupancy controlled dimming, ESL provides safety and energy savings with a clean, modern look.

10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

ESL	4	-			-	FA	W	-	ED	U	-		
MODEL	SIZE	COLOR TEMP	NOMINAL LUMENS[1]			LENS	DISTRIBUTION		DRIVER	VOLTAGE		OPTIONS	
ESL Escalate Stairwell Luminaire	4 4'	35 3500K 40 4000K 50 5000K	LW 4' (4100) ML 4' (4600) HL 4' (5800)			FA Frosted Acrylic	W Wide Distribution		ED 0–10V Dimming[2]	U 120–277V		ELL14 Emergency Battery Pack, 10W[3]	CONTROL OPTIONS NXOS NX, PIR BT Occupancy/Daylight Sensor, Round Ceiling Mount

[1] Nominal lumen output, refer to specification sheet Delivered Lumens table for exact values and available lumen outputs for fixture size
[2] External dimming leads not available
[3] For compatibility with Dual-Lite LiteGear® inverters in lieu of installed battery pack, contact Hubbell Lighting representative



CSL – LED Striplight*

The LED striplight brings together an economical price point and high performance.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	# on Pallet	DLC QPL
93075541	CSL4-4035	78531127442	LED, 4', 80 CRI, 3500K, 4231 LMS, Surface Mount or Pendant, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 40W, 105 LPW, White	●	●	●	●	4.9	120	●
93075542	CSL4-4040	78531127459	LED, 4', 80 CRI, 4000K, 4517 LMS, Surface Mount or Pendant, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 40W, 112 LPW, White	●	●	●	●	4.9	120	●
93075543	CSL8-8035	78531127466	LED, 8', 80 CRI, 3500K, 8460 LMS, Surface Mount or Pendant, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 81W, 105 LPW, White	●	●	●	●	10.8	120	●
93075544	CSL8-8040	78531127473	LED, 8', 80 CRI, 4000K, 9036 LMS, Surface Mount or Pendant, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 81W, 112 LPW, White	●	●	●	●	10.8	120	●



CS – Commercial Striplight

The CS is the fluorescent standard strip suitable for utility and light industrial or retail applications.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	# on Pallet
04141009F910000	CS4-132-EU	78531006280	Fluorescent, 4', Designed for 1-4' T8 Lamps, Ceiling Mount or Suspended, 120-277V T8 Electric Ballast, White			●	●	9	77
04241009F910000	CS4-232-EU	78531005016	Fluorescent, 4', Designed for 2-4' T8 Lamps, Ceiling Mount or Suspended, 120-277V T8 Electric Ballast, White		●	●	●	9	77
03441009H910000	CS8-232-4EU	78531005023	Fluorescent, 8', Designed for 4-4' T8 Lamps, Ceiling Mount or Suspended, (1) 4 Lamp T8 120-277V Electric Ballast, White		●	●	●	17	77
93038455	CS8-254-4EPU	78531022976	Fluorescent, 8', Designed for 4-4' T5HO Lamps, Ceiling Mount or Suspended, (1) 4 Lamp T5HO 120-277V Program Start Ballast, White				●	17	77
984084158000000	CSHC	78531000868	Chain Assembly, 14" (Pair)	●	●	●	●	0.2	

*DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.



CUC – Undercabinet Light

The Undercabinet luminaire is ideal for task lighting in general workspaces, breakrooms and copy rooms in commercial, institutional and government facilities.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	# on Pallet
93097056	CUC1-ED120	78531133580	LED, 1', Undercabinet, 90 CRI, 3000K, 366 LMS, Surface Mount, Polycarbonate Lens, 120V, 705W, 49 LPW, White	●	●			1	1536
93097057	CUC2-ED120	78531133597	LED, 2', Undercabinet, 90 CRI, 3000K, 724 LMS, Surface Mount, Polycarbonate Lens, 120V, 14W, 52 LPW, White	●	●			1.9	756
93097058	CUC3-ED120	78531133603	LED, 3', Undercabinet, 90 CRI, 3000K, 1099 LMS, Surface Mount, Polycarbonate Lens, 120V, 20W, 55 LPW, White	●	●			2.9	648
93097059	CUC4-ED120	78531133610	LED, 4', Undercabinet, 90 CRI, 3000K, 1248 LMS, Surface Mount, Polycarbonate Lens, 120V, 25W, 50 LPW, White	●	●			3.5	504
93097060	CUC-13CC	78531133627	Cord/Plug, 5', 120V	●	●				
93097061	CUC-24CC	78531133634	Connector Cable, 13"	●	●				
93097062	CUC-5F-120-CP	78531133641	Connector Cable, 24"	●	●				



CHB – Linear High Bay*

The CHB is an efficient and economical linear high bay suitable for a variety of areas including warehouses, gyms and mezzanines.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	# on Pallet	DLC QPL
93095151	CHB2-40LX-FA-EDU	78531133351	LED, 2', 80 CRI, 4000K, 11,380 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 88W, 130 LPW, White	●	●	●		10.6	44	●
93095155	CHB2-40MH-FA-EDU	78531133399	LED, 2', 80 CRI, 4000K, 21,949 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 172W, 127 LPW, White	●	●	●		10.6	44	●
93095153	CHB2-40ML-FA-EDU	78531133375	LED, 2', 80 CRI, 4000K, 17,013 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 133W, 128 LPW, White	●	●	●		10.6	44	●
93095157	CHB2-40MV-FA-EDU	78531133412	LED, 2', 80 CRI, 4000K, 27,343 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 212W, 129 LPW, White	●	●	●		13.4	22	●
93095152	CHB2-50LX-FA-EDU	78531133368	LED, 2', 80 CRI, 5000K, 11,483 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 88W, 131 LPW, White	●	●	●		10.6	44	●
93095156	CHB2-50MH-FA-EDU	78531133405	LED, 2', 80 CRI, 5000K, 22,038 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 172W, 128 LPW, White	●	●	●		10.6	44	●
93095154	CHB2-50ML-FA-EDU	78531133382	LED, 2', 80 CRI, 5000K, 17,105 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 132W, 130 LPW, White	●	●	●		10.6	44	●
93095158	CHB2-50MV-FA-EDU	78531133429	LED, 2', 80 CRI, 5000K, 27,522 LMS, Chain, Surface or Pendant Mount, Frosted Acrylic Lens, 0-10V Dimming Driver, 120-277V, 213W, 129 LPW, White	●	●	●		13.4	22	●

*DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.