

JEANETTE

HL1138201-AGB

Woven from natural wicker, the Jeanette table lamp channels the inviting spirit of cottagecore with a bold, sculptural silhouette. A textural shade rests on a matching body, with a rim of decorative Aged Brass glimmering at the base. Perfect for a console, end table, or bedside, Jeanette infuses any space with a dose of charm.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 21.5"

Width/Diameter: 20"

Canopy/Backplate: 8"

Product Weight: 9lb

Canopy/Backplate Shape: Cylinder

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Light Natural Wicker

Shade 1 Top Width: 5"

Shade 1 Bottom L/W: 0" / 20"

Shade 1 Height: 9.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 CREAM FABRIC

Switch Type: ON/OFF SWITCH ON SOCKET

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 23" x 23" x 20"

Carton 1 Weight: 15lb

Shipping Method: Ground

Country of Origin: VN

