



TEGERA® 70

Learn more

SLEEVE WITH CUT RESISTANCE LEVEL B

Cut protection sleeve with cut resistance level B. 13 gg knitted with CRF® technology, polyester, spandex and basalt fibre yarn. For all-round work and approved for handling foodstuffs. With unique hand-attachment for good fit and easy donning and doffing of gloves. Use together with a suitable glove for full protection.

CHARACTERISTICS

- Flexible
- Comfortable
- Breathable

FUNCTIONS

- Approved for handling foodstuffs
- Washable in 60° C

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Cut risk environments

PRIMARY AREAS OF USE

Assembly, Building and construction, Engineering, Food handling, Inspection work, Installation work, Machine operating, Metalwork, Warehouse work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Electrical equipment manufacturing, Food and beverage processing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant sleeves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL Basalt fibre thread, CRF® Technology, HPPE, Nylon, Polyester, Spandex
LENGTH 420-490 mm
COLOUR Black
PIECES PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Bulk pack
FASTENING Elasticated 360°
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 10 N
OUTER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Polyester, Basalt fibre thread, Nylon, Elastane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X4XB

ANSI A3 CUT

ANSI 4 ABR

FEATURES

Cut protection

Washable 60°C

SIZE		ARTICLE NUMBER	EAN
7	S	70-7	7340118407494
8	M	70-8	7340118341248
9	L	70-9	7340118341231
10	XL	70-10	7340118341255

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.