



PIP® Mega T-Fit™

T-Shape Disposable Soft Polyurethane Foam Ear Plugs - NRR 32 / SNR 37

- Innovative "T-Shape" makes removal simple
- Consistent cellular structure for optimal expansion recovery time for a consistent, uniform fit
- Smooth closed cell outer layer that prevents debris build-up
- Soft and comfortable PowerSoft™ foam supports all day comfort
- NRR 32 protection

Applications

- Construction Applications
- Manufacturing
- Workshops
- Energy

Technical Data

Color	Orange
Sizes Available	OS
Packaging	Boxed
Packed	10 Boxes/Case
Case Dimensions (in)	21.37 x 16.38 x 9.62
Case Weight (lbs)	10.30
Country of Origin	Mexico
Hearing Style	Uncorded
Ear Plug Material	Polyurethane Foam
Shape	T-Shape
Box Count	200
EN 352	EN352-2: Earplugs
Certifications	TAA Compliant

Performance Data

NRR Rating (ANSI S3.19-1974)	32
SNR Rating	37
SLC 80	22
SLC 80 Class	Class 4
Attenuation - High Frequency	37
Attenuation - Medium Frequency	34
Attenuation - Low Frequency	32

Care Instructions

These ear plugs are disposable, but when not in use should be kept in clean, dry condition.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
267-HPF510	Orange	OS	616314268670	2616314268678	02616314268678