

KS34, Split Bolt Connector, Run/Tap: 2/0 AWG Str-500 kcmil

By Burndy
Catalog # [KS34](#)



Copper Split Bolt, Cu: 2/0 AWG (Str)-500 kcmil (Run & Tap).

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Cables

Specifications

Certification - ETL	No
Certification - UL Recognized	N
Standards - RoHS Compliance Status	EX
Certification - cULus	N
Certification - UL Listed Direct Burial	Y
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rebar Size	6
Conductor - Rebar Size Range	6
Conductor - Copper Str Run Range	2/0 AWG-500 kcmil
Conductor - Copper Str Run	<ul style="list-style-type: none"> • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Solid Run Range	2/0 AWG-500 kcmil
Conductor - Copper Solid Run	<ul style="list-style-type: none"> • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Conductor - Copper Solid Tap Range 2/0 AWG-500 kcmil

- Conductor - Copper Solid Tap
- 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil
 - 400 kcmil
 - 450 kcmil
 - 500 kcmil

Conductor - CopperWeld Str Tap Range 19 #6

Conductor - CopperWeld Str Tap 19 #6

Conductor - CopperWeld Str Run Range 19 #6

Conductor - CopperWeld Str Run 19 #6

Conductor - CopperWeld Str Run 19 #6

- Conductor Type
- CU C Solid-Run
 - CU C Str-Run
 - CU Weld C Solid-Run
 - CU Weld C Str-Run
 - CU C Str-Tap
 - CU Weld C Solid-Tap
 - CU Weld C Str-Tap
 - CU C Solid-Tap

Conductor - Copper Str Tap Range 2/0 AWG-500 kcmil

- Conductor - Copper Str Tap
- 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil
 - 400 kcmil
 - 450 kcmil
 - 500 kcmil

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-31/100 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm
Dimension - Width inch	1.48 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	71 mm
Dimension - B Length inch	1.31 in

Dimension - Cross Flats inch 1.82 in
Dimension - Width fraction 1-12/25 in
Dimension - Length Overall inch 2.79 in

Material Copper
Plating Type Unplated
UPC 12 Digit 7818100145099

General

Plated No
Product Family Power Connectors>Split Bolts>KS
Trade Name SERVIT
Product Type Mechanical
UPC 781810014509
Type KS

Logistics

Minimum Pack Quantity 1
Pallet Quantity 1
Carton Quantity 12

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-KS34-SPEC-EN | REV 6/2026