



## YA342N, 500 kcmil, CU, 2 Hole NEMA, Long Barrel

By Burndy  
Catalog # [YA342N](#)

500 kcmil Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, Long Barrel, Tin Plated, Brown / 20 or 299 Index



### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

### Application

Wire Termination

### Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL486A-UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

### Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	500 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	500 kcmil

### Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2

Connector Type LONG BARREL

### Current

Voltage Rating	35 kV
Voltage - Maximum	35000

### Dimensions

Dimension - Pad Width inch	1.55 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	154 mm
Dimension - Outside Diameter inch	1.06 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	2-5/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-1/4 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	2.25 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	6.06 in

### General

Trade Name	HYLUG™
Die Index	20
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810506059
Type	Long Barrel, Tin Plated

Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810506059
UPC 14 Digit GTIN	00781810506059

Pallet Quantity	1728
Carton Quantity	54

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)  
[Installation Manual \[French, English\]](#)

### Logistics

Minimum Pack Quantity 6

---



A Hubbell brand