SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

**62-8042** - Titan; 32-Inch LED Pendant; 60 Watt; 2700K/3000K/3500K CCT; Smoked Bronze Finish; Alabaster Stone

90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 25,000 HOURS | 3 YEAR WARRANTY | 120-277V | IP 20

## GENERAL

| | |
|---|---|
| Company | NUVO |
| EA Height | 8.0 |
| EA Width | 35.4 |
| EA Length | 35.4 |
| Mounting Height | 1.5 |
| Bulb Included | Integrated |
| Diameter | 31.5 |
| Material | Stainless Steel |
| Includes | N/A |
| Status | Active |
| Style | Contemporary |
| Surge Protection | Built-in surge protection - 2KV |
| Total Harmonic Distortion | <20% |
| Up Down Installation | Down |
| CCT Selectable | Yes |
| Wattage Selectable | No |
| Collection | Titan |
| Finish Family | Bronze |
| Amps | 1.500A |
| Mounting Diameter | 7.25 |
| Lens Finish | Alabaster |
| Lens Material | Alabaster Stone |
| Lensed | Yes |
| Power Factor | >0.9 |
| Sloped Ceiling Compatible | Yes |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Incandescent Equivalent | 150W |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 2700K/3000K/3500K |
| Dimmable | Yes-Dimmable |
| Hours Rated | 25000 |
| Beam Angle (degree) | 120 |
| Color Temp | Warm White to Neutral White |
| CRI | 90+ |
| Dimming Type | Phase cut |
| Operating Frequency | 50/60Hz |
| Operating Temp | -4F to +140F (-20C to +60C) |
| Lumens | 4800L |
| Volts | 120V-277V |
| Watts | 60W |
| Connection | Hardwire |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | Smoked Bronze |
| Housing Color | Smoked Bronze |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Round |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 3-Years |
| Rated For Enclosed Fixture | No |

## FEATURES

| | |
|---|---|
| Flicker Free | Yes |

## PACKAGING

| | |
|---|---|
| UPC | 045923416606 |
| Case Cube | 5.8017 |
| Case Height | 8.0 |
| Case Length | 35.4 |
| Case Quantity | 1 |
| Case UPC | 10045923416603 |
| Case Weight | 47.6 |
| Case Width | 35.4 |
| EA Cube | 5.8017 |
| EA Height | 8.0 |
| EA Length | 35.4 |
| EA Quantity | 1 |
| EA Weight | 47.6 |
| EA Width | 35.4 |
| Pack Type | Kraft Box |
| Web Height | 3.5 |
| Web Width | 31.5 |

## COMPLIANCE

| | |
|---|---|
| Air Tight | No |
| CA Prop 65 | Lead |
| Dark Sky Rated | No |
| FCC Compliant | Yes |
| IC Rated | No |
| IP Rating | IP20 |
| Location Rating | Dry |
| NSF Approved | No |
| ROHS Compliant | Yes |
| Safety Listing | cETLus |
| California Ban | Lawful for sale |
| Energy Star Certified | No |
| Title 20 | Exempt |
| T24/JA8 Compliant | No |



© Satco Products, Inc.
All rights reserved 2026