

RIAN

PFL1055-PBR

Repetitive geometric shapes drawn from mid-century motifs create an eye-catching totemic stack in the Rian floor lamp. Each natural wicker bowl is individually lit, allowing a soft diffusion of light through the textural weave. With an impressive height of 55 inches, this 3-light floor lamp makes for a striking sculptural addition to any room.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 55"

Width/Diameter: 13.25"

Canopy/Backplate: 8.25"

Product Weight: 17.5lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Light Natural Wicker

Shade 1 Top Width: 13.25"

Shade 1 Height: 7.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A15

Max Wattage: 10

Bulb Quantity: 3

Bulb Included: No

Cord Type: SPT-2 BLACK FABRIC

Dimmer Type: Incandescent

Switch Type: ON/OFF STOMP SWITCH

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 16" x 16" x 59"

Carton 1 Weight: 25lb

Shipping Method: Truck Only

Country of Origin: VN

