



JSP® Evolution® Deluxe 6161

Full Brim Mining Hard Hat with HDPE Shell, 6-Point Polyester Suspension, Wheel Ratchet Adjustment and CR2 Reflective Kit

- Mining lamp bracket is non-corrosive and will receive 99% of the "World's Mining Lamps"
- Cable loop located on the rear of the hard hat keeps the cable in place
- Class R2 high intensity reflective material offers 360° reflective coverage and significantly more reflectivity than standard reflective clothing material
- High-Density Polyethylene (HDPE) shell with a full brim providing additional protection against sun, glare, rain and falling debris
- Extended back brim helps protect neck and ears from the sun's UV rays, as well as a run-off for rain and snow...short front brim shades the face while allowing excellent visibility
- Brim includes finger grips on front and rear, as well as a textured underside to reduce reflection/glare
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Red, White, Blue, Black, Gray, Yellow, Neon Yellow, Neon Orange, Green
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	21.65 x 12.60 x 17.91
Case Weight (lbs)	10.36
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Sweatband	Chamlon
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6161MCR2-11	Black	OS	616314253355	10616314962094	02616314253353
280-EV6161MCR2-50	Blue	OS	616314164668	01616314164667	02616314164666
280-EV6161MCR2-40	Gray	OS	616314438707	10616314438704	20616314438701
280-EV6161MCR2-30	Green	OS	616314167157	01616314167156	02616314167155
280-EV6161MCR2-OR	Neon Orange	OS	616314165573	01616314165572	02616314165571
280-EV6161MCR2-LY	Neon Yellow	OS	616314444241	10616314444248	20616314444245
280-EV6161MCR2-60	Red	OS	616314170294	01616314170293	02616314170292
280-EV6161MCR2-10	White	OS	616314153587	01616314153586	02616314153585
280-EV6161MCR2-20	Yellow	OS	616314164644	01616314164643	02616314164642