PRODUCT INFORMATION PACKET

Model No: D131
Catalog No: D131
Fan and Blower Motor, 1/40 HP, 1 Ph, 60 Hz, 115 V, 1500 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Phase	1	Output HP	1/40 Hp
Output KW	0.02 kW	Voltage	115 V
Speed	1500 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.00 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	5.97 in
Frame Length	3.13 in	Shaft Diameter	0.313 in
Shaft Extension	2.30 in		
Connection Drawing	NA	Outline Drawing	7163507915_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/06/2026

Uncontrolled Copy

BROWNING MANUFACTURING COMPANY, MAYSVILLE, KENTUCKY

DATE	4-9-65
DR.	BL.
CH'K'D	
DISTRIBUTION	

8.000 O.D. 2 GR "B", 3.500 O.D. 4 GR "B" x 1 5/8 B. SPCL. STEPCONE SHEAVE

NEW YORK AIR BRAKE CO.

MATERIAL 8 1/2" C.I. STICK

PART NO.

BALANCE "STD.

FINISH "STD. GRAY"

MARKING — YES: 7 7 — NO: 7

BROWNING

SIZE


PART NO.

TOLERANCES
UNLESS OTHERWISE SPECIFIED
FRACTIONAL DIMENSIONS ±1/64
DECIMAL DIMENSIONS ±.005

REVISION | BY | DATE

REVISION | BY | DATE

REVISION | BY | DATE



APPROVAL	NO APPROVAL REQUIRED	DWG. NO.	ISSUE
SENT TO EDWARDS IND.		NA-3002	
SENT 4/9/65 RET'D 4-14	PER DATE		

FORM 14C