

Product Specifications



#8 x 1/4" Slotted Hex Washer Head Sheet Metal Screw (Tuff Pack)

Part Number HWSMST814

UPC 781002863243



Sheet Metal Screws are a versatile fastener with specially hardened spaced threads and sharp points, and are capable of tapping their own internal threads. Typical applications for Sheet Metal Screws include fastening light metal sheets, wood, and plastic. They are manufactured with case hardened steel and finished with a zinc plating. ASME B18.3 covers the general requirements for the dimensions and performance of Steel Sheet Metal Screws.

Physical Characteristics

Type	Sheet Metal Screw
Drive Type	Slotted
Head Type	Hex Washer
Thread Type	AB
Point Type	AB
Size	#8 x 1/4"
Dia./Thread Size	#8
Hex Size	1/4"
Head Diameter	0.322" - 0.348"
Length (in)	1/4"
Head Height	0.096" - 0.110"
Thread Pitch\Thread Per Inch	18
Material	Carbon Steel
Finish	Zinc Plated

Performance Data

Rockwell Hardness	HRC 28 - 38
Special Features	Combo Hex Head, Zinc Plated, Corrosion Resistant
Applications	Light Metal Sheets, Wood, and Plastic

Packaging Details

Standard Qty	500
Master Qty	3000
Price Per	100
Package Length	3.80
Package Width	3.90
Package Height	3.60
Package Weight	.70

Certifications

UNSPSC	31161506
RoHS Compliant	Yes
Meets/Exceeds	ASME B18.6.3

L.H. Dottie Co. Commerce, CA 323-725-1000 www.lhdottie.com