



P65

Technical Data



Bouton® Optical Zenon Ultra-Lyte™

Rimless Safety Glasses with Clear Temples, Clear Lens and Anti-Scratch Coating

- Squared lens shape with a slight taper, provides modern styling for the wearer
- Ultra-lightweight design conforms to the head promoting all-day wear
- Spring fit temples offers a comfortable fit that conforms to the head
- Molded nose bridge design to fit the vast majority of users
- 10 Base curve lens
- Meets ANSI Z87.1-2020 standards
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Color	Clear
Sizes Available	OS
Packaging	Bagged Pair
Packed	144 Pair/Case
Case Dimensions (in)	20.08 x 11.42 x 18.31
Case Weight (lbs)	11.02
Country of Origin	Taiwan
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Bayonet
Base Curve	10
Construction	Womans Fit
Certifications	ANSI Z87.1, TAA Compliant

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-14-0000	Clear	Clear	Clear	AS	616314736704	10616314736701	20616314736708
250-14-0001	Gray	Tinted	Gray	AS	616314736148	10616314736145	20616314736142
250-14-0009	Amber	Tinted	Amber	AS	616314736346	10616314736343	20616314736340
250-14-0020	Clear	Clear	Clear	AF/AS	616314736186	10616314736183	20616314736180
250-14-0021	Gray	Tinted	Gray	AF/AS	616314736223	10616314736220	20616314736227
250-14-0520	Clear	Clear	Clear	AS/FL360	616314736261	10616314736268	20616314736265
250-14-0521	Gray	Tinted	Gray	AS/FL360	616314736308	10616314736305	20616314736302
250-14-0529	Amber	Tinted	Amber	AS/FL360	616314736384	10616314736381	20616314736388

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated