

YSR312CFXLTCKITC

Attributes	Values
Application	Wire Reducing Splice
AWG Size	350 kcmil - 2 AWG
Barrel Style	Skived
Barrel Type	Standard
Coating	Tin-Plated
Collection Name	HYREDUCER
Color Code	Red/Brown
Cond. Material	Copper
CSA Approved	No
cUL Approved	No
cULus Approved	No
Die Index	18;10
ETL Approved	No
Height (in)	0.46
Length (in)	3.37
Length L2 (in)	1.49
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Power Cond. AWG Size	350 KCMIL-2 AWG
Strip Length (in)	1.41
Temperature Rating	194 Deg C
Voltage	35 kV
Width (in)	0.88