



## Ironcat®

AR Top Grain Cowhide Leather Drivers Glove  
with Split Cowhide Back and Para-Aramid Lining  
- Keystone Thumb

- Top Grain Split Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Top Grain leather palm is smooth, provides durability and dexterity
- Bourbon brown split cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Para-Aramid blend lining provides added cut and heat resistance
- Keystone thumb is ergonomic, reduces hand fatigue, offers superior dexterity and durability
- ARC Rating: 27 cal/cm2
- PPE 3 (HRC 3)
- Sewn with Kevlar® for maximum seam strength
- Drivers gloves feature slip-on styling to provide good fit and comfort
- Elastic closure sewn inside glove for safety and comfort



## Technical Data

|                      |                          |
|----------------------|--------------------------|
| Color                | Brown                    |
| Sizes Available      | S-3XL                    |
| Packaging            | Pair Tagged Retail Ready |
| Packed               | 72 Pair/Case             |
| Case Dimensions (in) | 18.03 x 14.02 x 20.98    |
| Case Weight (lbs)    | 40.30                    |
| Country of Origin    | Pakistan                 |
| Hide                 | Top Grain Cowhide        |
| Lining               | Aramid                   |
| Grade                | Premium                  |
| Cuff                 | Slip-on                  |
| Palm                 | Leather                  |
| Back                 | Split Cowhide Leather    |
| Closure              | Slip On                  |
| Thumb                | Keystone                 |
| Stitching            | Kevlar                   |
| Construction         | Gunn Cut, Cut-and-Sewn   |

## Performance Data

|                     |            |
|---------------------|------------|
| ARC Rating          | 27 cal/cm2 |
| ARC Rating          | 27 cal/cm2 |
| Cut Level           | A4         |
| Cut Level           | A4         |
| ANSI Puncture Level | 3          |
| ANSI Puncture Level | 3          |

## Care Instructions



Do Not Wash

## SKU Information

| SKU       | COLOR | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|-----------|-------|------|--------------|----------------|----------------|
| 9444/S    | Brown | S    | 616314369537 | 10616314369534 | 20616314369531 |
| 9444/M    | Brown | M    | 616314375118 | 10616314375115 | 20616314375112 |
| 9444/L    | Brown | L    | 616314369452 | 10616314369459 | 20616314369456 |
| 9444/XL   | Brown | XL   | 616314369575 | 10616314369572 | 20616314369579 |
| 9444/XXL  | Brown | 2XL  | 616314375033 | 10616314375030 | 20616314375037 |
| 9444/XXXL | Brown | 3XL  | 616314375071 | 10616314375078 | 20616314375075 |