SATCO® | NUVO®

Project / Job Name:

Location:

Fixture Type:

Notes:



65-695 - 2X4 Double Basket LED Troffer Fixture; Wattage Selectable; CCT Selectable; Lumens Selectable; 100-277V; White Finish

DAMP LOCATION · DIMMABLE · FC · RoHS COMPLIANT · CCT SELECTABLE · 50,000 HOURS · IP 20 · IC RATED · 0-10V DIMMING

GENERAL

Company	NUVO
EA Height	25.67
EA Width	3.27
EA Length	49.49
Bulb Included	Integrated
Material	Steel
Fixture Type	Double Basket Troffer
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Amps	0.300-0.108/0.400-0.144/0.500-0.181A
Has Camera	No
IOT Enabled	No
Lens Material	Poly methyl methacrylate (PMMA)
Power Factor	0.9
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	125W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Warm to Cool White
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-4F to +104F (-20C to +40C)
HID Equivalent	70W-125W
Lumens	3300L-5750L
Volts	120V-277V
Watts	30W/40W/50W
Max Lumens	5750L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923655203
Case Cube	2.4041
Case Height	25.67
Case Length	49.49
Case Quantity	1
Case UPC	10045923655200
Case Weight	16.1
Case Width	3.27
EA Cube	2.4041
EA Height	25.67
EA Length	49.49
EA Quantity	1
EA Weight	16.1
EA Width	3.27
Pack Type	Box
Web Height	2.61
Web Length	47.72
Web Width	23.74

COMPLIANCE

CA Prop 65	Lead
DLC ID	S-MTPRWN
FCC Compliant	Yes
IC Rated	Yes
IP Rating	IP20
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
UL Application	LED Recessed Luminaire/Type IC
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026