

# BELLUNO

533-40-VGL

Airy and textural, Belluno's tiered composition pairs sculptural volume with a lightness of material. Made from pleated white paper, each layer brings a soft sense of translucency and movement. The Vintage Gold Leaf finish on the chain, ceiling canopy, and lower cap adds an elegant contrast to the crisp white folds. Available as a 2-light and 3-light chandelier, Belluno sets a soft ambience as light shines through its paper construction.

\*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

## FINISHES

### VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

## DIMENSIONS

Height: 28.25"

Width/Diameter: 40"

Minimum Height: 32"

Maximum Height: 102.25"

Canopy/Backplate: 6.5"

Hanging Type: 72" Chain

Product Weight: 9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

## Shade

Shade 1: Textile

Shade 1 Finish: Handmade Paper

Shade 1 Top Width: 24.75"

Shade 1 Bottom L/W: 0" / 5.75"

Shade 1 Height: 7.75"

Shade 2: Textile

Shade 2 Finish: Handmade Paper

Shade 2 Top Width: 32.5"

Shade 2 Bottom L/W: 0" / 5.5"

Shade 2 Height: 9.5"



## ELECTRICAL



### Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 3

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND  
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

## SHIPPING

Carton 1: 44" x 44" x 38"

Carton 1 Weight: 42lb

Shipping Method: Truck Only

Country of Origin: PH