

# ALORA

1286-VGL/GLI

Architectural and sleek, but with an artful, botanical flourish, Alora has strong modern design appeal. While the framework features clean lines and right angles, the scalloped floral shades have an irregular, hand-sculpted quality. A textural relief pattern on the surface of the shades adds visual interest. Alora is available in multiple formats and 3 finish options.

## FINISHES

VINTAGE GOLD LEAF w/ Gilded Ivory

Coastal Suitable Finish (EPM): No

## DIMENSIONS

Height: 28.5"

Width/Diameter: 32"

Minimum Height: 33"

Maximum Height: 87.25"

Canopy/Backplate: 8.5"

Hanging Type: 1-3" / 1-6" / 1-12" / 2-18" Stems

Product Weight: 12.1lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

## Shade

## ELECTRICAL



### Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: G25

Max Wattage: 15

Bulb Quantity: 6

Bulb Included: No

Wire Length: 120"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

## SHIPPING

Carton 1: 37" x 37" x 33"

Carton 1 Weight: 29lb

Shipping Method: Truck Only

Country of Origin: PH

