

LED filament lamps

Decorative - Candelabra base/torpedo



S29877, S29866, S29920,
S29922, S29890, S8839,
S9960, S9961, S21708,
S21729
C11/B11



S9868
C11



S21708,
S21729
B11



LED Decorative Filament Lamps - Candelabra Base - Torpedo Shape



Item Number	Lamp Description	W	Bulb Type	Base	V	Finish	CCT	Lm	CRI	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
25 Watt Replacement													
S29920*	2.5W CTC/LED/CL/27K/120V	2.5	C11	E12	120	Clear	2700K	200	80	3 7/8	15K	045923299209	24/6
40 Watt Replacement													
S9868	3.5CTF/LED/FR/27K/120V	3.5	C11	E12	120	Frosted	2700K	350	80	4 5/16	15K	045923098680	24/6
S29922*	4W CTC/LED/27K/CL/120V	4	C11	E12	120	Clear	2700K	350	80	3 7/8	15K	045923299223	24/6
S29890*	4W CTC/LED/30K/CL/120V	4	C11	E12	120	Clear	3000K	350	80	3 7/8	15K	045923298905	24/6
S8839*	4W CTC/LED/40K/CL/120V	4	C11	E12	120	Clear	4000K	350	80	3 7/8	15K	045923088391	24/6
S29866*	4W CTC/LED/50K/CL/120V	4	C11	E12	120	Clear	5000K	350	80	4 5/16	15K	045923298660	24/6
60 Watt Replacement													
S9960*	5.5W CTC/LED/27K/CL/120V	5.5	C11	E12	120	Clear	2700K	500	80	3 7/8	15K	045923099601	24/6
S9961*	5.5W CTC/LED/30K/CL/120V	5.5	C11	E12	120	Clear	3000K	500	80	3 7/8	15K	045923099618	24/6
S9964*	5.5W ETC/LED/27K/CL/120V	5.5	C11	E26	120	Clear	2700K	500	80	3 1/2	15K	045923099649	24/6
Multi-Pks													
S21708*	4.5W CTC/LED/27K/CL/120V/3Pk	4.5	B11	E12	120	Clear	2700K	350	80	3 7/8	15K	045923217081	12/3Pks
S21729*	4.5W CTC/LED/3K/CL/120V/3Pk	4.5	B11	E12	120	Clear	3000K	350	80	3 7/8	15K	045923217296	12/3Pks
90 CRI—CEC/T20 - 40 Watt Replacement													
S29877*■	4.5WCTC/LED/927/120/E12	4.5	B11	E12	120	Clear	2700K	350	90	3 3/4	15K	045923298776	24/6
S11369*	4.5CTF/LED/927/120V/E12	4.5	B11	E12	120	Frosted	2700K	360	90	3 3/4	15K	045923113697	24/6
S11370*	4.5CTC/LED/930/120V/E12	4.5	B11	E12	120	Clear	3000K	360	90	3 3/4	15K	045923113703	24/6
90 CRI—CEC/T20 - 60 Watt Replacement													
S11371*	5.5CTC/LED/927/120V/E12	5.5	B11	E12	120	Clear	2700K	500	90	3 3/4	15K	045923113710	24/6
S11373*	5.5CTF/LED/927/120V/E12	5.5	B11	E12	120	Frosted	2700K	500	90	3 3/4	15K	045923113734	24/6
S11372*	5.5CTC/LED/930/120V/E12	5.5	B11	E12	120	Clear	3000K	500	90	3 3/4	15K	045923113727	24/6

■ Also T24 compliant. JA8-2019

Product sheet SA1980

**See warranty for details.