



PIP® V1™

V1 Passive Ear Muff with Adjustable Headband - NRR 23

- Dielectric, metal-free earmuffs suitable for use in workplace environments with exposure to electrical voltage
- Smooth telescopic size adjustment for precise and stable fit
- Slim stirrup design reduces the risk of snagging in confined areas
- Extra soft memory foam ear cushions and ultra low weight padded headband provide optimum comfort even when worn for extended periods
- Bright Color coding with v1™, v2™, v3™ noise protection indicator for easy selection and identification
- Replacement hygiene kits available separately

Technical Data

Color	Neon Green
Sizes Available	OS
Packaging	Boxed
Packed	20 Pair/Case
Case Dimensions (in)	22.44 x 12.20 x 16.54
Case Weight (lbs)	14.37
Country of Origin	China
Hearing Style	Headband
Protection Type	Passive
Construction	Dielectric
Product Circularity	Reusable / Launderable

Performance Data

NRR Rating (ANSI S3.19-1974)	23
SLC 80 Class	Class

Care Instructions

Routinely wash with mild soap and water. Allow cushions to air dry.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
263-V1HB	Neon Green	OS	616314725708	10616314725705	20616314725702