

GARETH

B6730-PBR/TBK

Drawing inspiration from traditional lanterns, this family of sleek exterior fixtures includes sconce and a portable lantern in multiple sizes. Elongated silhouettes and a mixed-finish combination of Textured Black and Patina Brass give these lanterns a contemporary update. While Gareth is equipped with a single chunky pillar candle for a timeless look, the light source is actually a lightweight aluminum puck with LED technology housed the bottom of the glass cylinders. Gareth is available as both a sconce and a portable lantern in multiple sizes. The portable option is rechargeable and includes a convenient handle for easy transport.

FINISHES

PATINA BRASS w/ TEXTURE BLACK

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 29.25"

Width/Diameter: 8.25"

Canopy/Backplate: 8.25"

Product Weight: 15.44lb

Extension: 9"

Top to Center: 7.5"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Glass

Shade 1 Finish: Clear

Shade 1 Top Width: 7.5"

Shade 1 Height: 22.25"

Shade 2: Glass

Shade 2 Finish: Clear

Shade 2 Top Width: 7.75"

Shade 2 Height: 22.25"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 13

Bulb Quantity: 1

Bulb Included: Yes

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 3000k

Lumens: 475

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 17" x 17" x 37"

Carton 1 Weight: 21lb

Shipping Method: Ground

Country of Origin: CN



HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993

REVISED 3.11.2022