


### Type C Set Screw Type



Allows access to the interior of a conduit system for inspection, pulling and maintenance.

 File No. E11077

#### Aluminum


| Catalog Number | Trade Size | Unit Qty. | Std. Pkg. |
|----------------|------------|-----------|-----------|
| C-31           | 1/2"       | 10        | 60        |
| C-32           | 3/4"       | 10        | 60        |
| C-33           | 1"         | 5         | 30        |
| C-34           | 1 1/4"     | 2         | 10        |
| C-35           | 1 1/2"     | 2         | 10        |
| C-36           | 2"         | 1         | 6         |
| C-37CG*        | 2 1/2"     | ---       | 1         |
| C-38CG*        | 3"         | ---       | 1         |
| C-39CG*        | 3 1/2"     | ---       | 1         |
| C-40CG*        | 4"         | ---       | 1         |


\*Provided with cover and neoprene gasket.

### Combination Type C



Units have a threaded interior for use with rigid or IMC as well as set screws for use with EMT. Preassembled with cover and neoprene gasket. NPT Threads. NEMA TYPE 2,3,3R & 4.

 File No. E11077

 Listed Raintight when used with rigid conduit or raintight compression connectors.


#### Aluminum with Cover and Gasket

| Catalog Number | Trade Size | Unit Qty. | Std. Pkg. |
|----------------|------------|-----------|-----------|
| C-41CGC        | 1/2"       | 10        | 60        |
| C-42CGC        | 3/4"       | 10        | 60        |
| C-43CGC        | 1"         | 5         | 30        |
| C-44CGC        | 1 1/4"     | 2         | 10        |
| C-45CGC        | 1 1/2"     | 2         | 10        |
| C-46CGC        | 2"         | 1         | 6         |

### Type LB Set Screw Type



Allows access to the interior of a conduit system for inspection, pulling and maintenance.

 File No. E11077

#### Aluminum

| Catalog Number | Trade Size | Unit Qty. | Std. Pkg. |
|----------------|------------|-----------|-----------|
| LB-31          | 1/2"       | 10        | 60        |
| LB-32          | 3/4"       | 10        | 60        |
| LB-33          | 1"         | 5         | 30        |
| LB-34          | 1 1/4"     | 2         | 10        |
| LB-35          | 1 1/2"     | 2         | 10        |
| LB-36          | 2"         | 1         | 6         |
| LB-37          | 2 1/2"     | ---       | 1         |
| LB-38          | 3"         | ---       | 1         |
| LB-39          | 3 1/2"     | ---       | 1         |
| LB-40          | 4"         | ---       | 1         |