



Project / Job Name:

Location:

Fixture Type:

Notes:

65-1605 - 1X4 LED Single Basket Troffer; Emergency Battery; Field Selectable; 120-277 Volt; White Finish



GENERAL

Company	NUVO
EA Height	12.52
EA Width	1.77
EA Length	48.62
Bulb Included	Integrated
Material	Steel
Fixture Type	Troffer
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Amps	0.070-0.340A
Has Camera	No
Integrated Features	Intergrated Battery Backup
IOT Enabled	No
Lens Finish	White
Lens Material	Polycarbonate (PC)
Lensed	Yes
Power Factor	0.9
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	200W

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Neutral White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	2500L/3750L/5000L
Volts	120V-277V
Watts	20W/30W/40W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923516054
Case Cube	0.6235
Case Height	12.52
Case Length	48.62
Case Quantity	1
Case UPC	10045923516051
Case Weight	10.71
Case Width	1.77
EA Cube	0.6235
EA Height	12.52
EA Length	48.62
EA Quantity	1
EA Weight	10.71
EA Width	1.77
Pack Type	Box
Web Height	1.55
Web Length	47.76
Web Width	11.93

COMPLIANCE

CA Prop 65	Lead
DLC ID	S-C84GCB; S-CGXSC2
FCC Compliant	Yes
IC Rated	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Yes
T24/JA8 Compliant	No