

SOLARA

555-17-VPB

Solara captures the quiet poetry of a solar system in motion; celestial, geometric, and gently luminous. Inspired by constellations, each cloud seedy glass shade glows like a radiant star, suspended in orbit by slender rods finished in Vintage Patina Brass. The 3- and 5-light chandeliers feature diamond-shaped shades that create dimensionality from every perspective, while the single-light pendant drops like a sculptural earring. The result is lighting that feels both architectural and romantic. They are designed not just to illuminate, but to bring a sense of wonder to the everyday.

FINISHES

VINTAGE POLISHED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 30.25"

Width/Diameter: 16.5"

Canopy/Backplate: 4.75"

Hanging Type: 2-9" Stems

Product Weight: 4lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Seeded Cloud

Shade 1 Top Width: 12"

Shade 1 Height: 14.75"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 144"

Cord Type: LOW VOLTAGE DC WIRE

Dimmer Type: TRIAC

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 625

Title 24: No

Field Serviceable: Yes



SHIPPING

Carton 1: 17" x 17" x 18"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: VN