

Circuit breakers

Circuit breakers for use with distribution panelboard kits

Breaker type QP

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
10	Q110	Q210	Q315
15	Q115	Q215	Q320
20	Q120	Q220	Q325
25	Q125	Q225	Q330
30	Q130	Q230	Q335
35	Q135	Q235	Q340
40	Q140	Q240	Q345
45	Q145	Q245	Q350
50	Q150	Q250	Q360
60	Q160	Q260	Q370
70	Q170	Q270	Q380
80	-	Q280	Q390
90	-	Q290	Q3100
100	-	Q2100	-
110	-	Q2110	-
125	-	Q2125	-

Breaker type HQP

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
15	Q115HH	Q215HH	Q315HH
20	Q120HH	Q220HH	Q320HH
25	Q125HH	Q225HH	Q325HH
30	Q130HH	Q230HH	Q330HH
35	Q135HH	Q235HH	Q335HH
40	Q140HH	Q240HH	Q340HH
45	Q145HH	Q245HH	Q345HH
50	Q150HH	Q250HH	Q350HH
60	Q160HH	Q260HH	Q360HH
70	Q170HH	Q270HH	Q370HH
80	-	Q280HH	Q380HH
90	-	Q290HH	Q390HH
100	-	Q2100HH	Q3100HH
110	-	Q2110HH	-
125	-	Q2125HH	-

Breaker type ED4

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
60	-	QJ22B060	QJ23B060
70	-	QJ22B070	QJ23B070
80	-	QJ22B080	QJ23B080
90	-	QJ22B090	QJ23B090
100	-	QJ22B100	QJ23B100
110	-	QJ22B110	QJ23B110
125	-	QJ22B125	QJ23B125
150	-	QJ22B150	QJ23B150
175	-	QJ22B175	QJ23B175
200	-	QJ22B200	QJ23B200
225	-	QJ22B225	QJ23B225

Breaker type QPH

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
15	Q115H	Q215H	Q315H
20	Q120H	Q220H	Q320H
25	Q125H	Q225H	Q330H
30	Q130H	Q230H	Q340H
35	Q135H	Q235H	Q350H
40	Q140H	Q240H	Q360H
45	Q145H	Q245H	Q370H
50	Q150H	Q250H	Q390H
60	Q160H	Q260H	Q3100H
70	Q170H	Q270H	-
80	-	Q280H	-
90	-	Q290H	-
100	-	Q2100H	-
110	-	Q2110H	-
125	-	Q125H	-

Breaker type ED4

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
15	ED41B015	ED42B015	ED43B015
20	ED41B020	ED42B020	ED43B020
25	ED41B025	ED42B025	ED43B025
30	ED41B030	ED42B030	ED43B030
35	ED41B035	ED42B035	ED43B035
40	ED41B040	ED42B040	ED43B040
45	ED41B045	ED42B045	ED43B045
50	ED41B050	ED42B050	ED43B050
60	ED41B060	ED42B060	ED43B060
70	ED41B070	ED42B070	ED43B070
80	ED41B080	ED42B080	ED43B080
90	ED41B090	ED42B090	ED43B090
100	ED41B100	ED42B100	ED43B100

Breaker type QJH2

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
60	-	QJH22B060	QJH23B060
70	-	QJH22B070	QJH23B070
80	-	QJH22B080	QJH23B080
90	-	QJH22B090	QJH23B090
100	-	QJH22B100	QJH23B100
110	-	QJH22B110	QJH23B110
125	-	QJH22B125	QJH23B125
150	-	QJH22B150	QJH23B150
175	-	QJH22B175	QJH23B175
200	-	QJH22B200	QJH23B200
225	-	QJH22B225	QJH23B225

Breaker type QJ2H

Ampere rating	Catalog number		
	1-Pole	2-Pole	3-Pole
60	-	QJ22B060H	QJ23B060H
70	-	QJ22B070H	QJ23B070H
80	-	QJ22B080H	QJ23B080H
90	-	QJ22B090H	QJ23B090H
100	-	QJ22B100H	QJ23B100H
110	-	QJ22B110H	QJ23B110H
125	-	QJ22B125H	QJ23B125H
150	-	QJ22B150H	QJ23B150H
175	-	QJ22B175H	QJ23B175H
200	-	QJ22B200H	QJ23B200H
225	-	QJ22B225H	QJ23B225H