



JSP® Evolution® Deluxe 6151

Standard Brim Mining Hard Hat with HDPE Shell,
6-Point Polyester Suspension and Wheel Ratchet
Adjustment

- Mining lamp bracket is non-corrosive and will receive 99% of the "World's Mining Lamps"
- Cable loop located on the rear of the hard hat keeps the cable in place
- High-Density Polyethylene (HDPE) shell designed with five raised channels running across the top for strength, and an extended back area for extra protection
- 6-Point polyester textile suspension system offers unrivaled comfort without compromising performance
- Unique "3D Adjustment" provides a precise fit using harness depth settings...unlike any other hard hat on the US market today
- Evolution Wheel Ratchet is easy to use and creates a firm comfortable fit
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



P65

Technical Data

Color	Neon Orange, Black, Neon Yellow, Blue, Yellow, White, Green, Red
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	23.03 x 9.45 x 18.01
Case Weight (lbs)	8.82
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Sweatband	Chamlon
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6151M-11	Black	OS	198987065508	10198987065505	20198987065502
280-EV6151M-50	Blue	OS	616314164583	01616314164582	02616314164581
280-EV6151M-30	Green	OS	616314185816	01616314185815	02616314185814
280-EV6151M-OR	Neon Orange	OS	616314169144	01616314169143	02616314169142
280-EV6151M-LY	Neon Yellow	OS	616314164682	01616314164681	02616314164680
280-EV6151M-60	Red	OS	616314164590	01616314164599	02616314164598
280-EV6151M-10	White	OS	616314153556	01616314153555	02616314153554
280-EV6151M-20	Yellow	OS	616314164576	01616314164575	02616314164574